




NOTES:

1. SUBSTRATE
BOROFLOAT®
2. COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)
 T(AVG) <1.0% @ 390 - 570nm
 T(AVG) >85% @ 620 - 750nm
 T(ABS) <2.0% @ 415 - 550nm
 T(ABS) >80% @ 630 - 750nm

3. CUT AND SEAM

4. ROHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
CLEAR APERTURE	≥85 %	≥85 %
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



TITLE	50 x 50 RED DICHROIC FILTER	
DWG NO	30634	SHEET 1 OF 1