



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



47661INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 39.523
GD RADIUS : 104.333
SCALE BAR : 400


SPOT DIAGRAM

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

REFERENCE : CHIEF RAY

47661INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 123.6490 μm
DIFFRACTION LIMITED RANGE: 5.999 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT

47661INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 200.000 \mu\text{m}$.
0.486 0.587 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

47661INK
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

EO Edmund
optics | worldwide

www.edmundoptics.com