



NOTES:

1. ALLOWABLE OPTICAL MATERIAL: GRADE A FINE ANNEALED
SCHOTT: N-BK7
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 ARCMIN
3. COATING (APPLY ACROSS COATING APERTURE)
S1: NONE
S2: NONE

4. SIX SIDEWALLS:
SURFACE ACCURACY: COMMERCIAL POLISH



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING**



	S1	S2			TITLE	15.0mm HEX LIGHT PIPE, 300mm lg
SHAPE	PLANO	PLANO	EFL (AT 587.6nm)	NA	DWG NO	84534
SURFACE ACCURACY AT 632.8nm	5 WAVES	5 WAVES	BFL (AT 587.6nm)	NA		
SURFACE QUALITY	60 - 40	60 - 40	ALL DIMS IN	mm		