





FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. 001 | S1 | S2 |
|--------------------------------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SPECTRAL TRANSMITTANCE $t_p(\%)$ | 93 | 93 |
| PASSBAND LIMIT 1 λ_{p1} (nm) | 750 | 750 |
| CUT-OFF POSITION λ_c (nm) | 720±9 | 720±9 |
| STOPBAND LIMIT λ_s (nm) | 648 | 648 |
| WAVELENGTH | IR | IR |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |



ALL DIMS IN

mm

TITLE

Ø25.4mm, HOYA R-72 LONGPASS FILTER

DWG NO

66057

SHEET
1 OF 1