




NOTES:

1. SUBSTRATE MATERIAL
SCHOTT: N-BK7 517/642
2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: NONE
S2: NIR I
Ravg ≤ 0.5% @ 600 - 1050nm

3. FINE GRIND SURFACE

4. RoHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A | S1 | S2 |
|------------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| ANGLE TOL. | ±15 | ±15 |
| SURFACE QUALITY | 40-20 | 40-20 |
| SURFACE FLATNESS | λ/8 | λ/8 |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

THIRD ANGLE PROJECTION



ALL DIMS IN

mm

EO® Edmund Optics®

TITLE

15mm, NIR I COATED, BBAR COATED RIGHT ANGLE PRISM

DWG NO

84524

SHEET
1 OF 1