



NOTES:

1. SUBSTRATE:  
N-BK7
2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
3. COATING (APPLY ACROSS CLEAR APERTURE)  
S1 & S2: RABS ≤0.25% @ 880nm  
RAVG ≤1.25% @ 400 - 870nm  
RAVG ≤1.25% @ 890 - 1000nm

4. FINE GRIND SURFACE

5. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                 | S1                   | S2                   |
|-----------------|----------------------|----------------------|
| SHAPE           | PLANO                | PLANO                |
| SURFACE QUALITY | 60-40                | 60-40                |
| CLEAR APERTURE  | Ø22.50               | Ø22.50               |
| BEVEL           | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |



ALL DIMS IN mm

**EO**® Edmund Optics®

TITLE

25mm DIA., 4mm THICK, VIS-NIR COATED  
λ/4 N-BK7 WINDOW

DWG NO

45661

SHEET  
1 OF 1