

NOTES:


1. SUBSTRATE: N-BK7
2. COATING (APPLY ACROSS COATING APERTURE)

S1: UNCOATED

S2: UNCOATED

 FINE GRIND SURFACE

4. SURFACE S2 TO BE PARALLEL TO SURFACE S1 WITHIN 30 ARCSEC
5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
6. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	90%	90%
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN

mm

 **Edmund Optics®**

TITLE

40mm DIAMETER UNCOATED, ULTRA-THIN N-BK7 WINDOW

DWG NO

66190

SHEET
1 OF 1