




NOTES:

- 1. SUBSTRATE: BOROFLOAT®
- 2. COATING (APPLY ACROSS CLEAR APERTURE):
S1 & S2: R(AVG) <1.0% @ 700 - 1150nm
- 3. FINE GRIND SURFACE
- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE FLATNESS	4 - 6λ	4 - 6λ
SURFACE QUALITY	80-50	80-50
CLEAR APERTURE	Ø27.00	Ø27.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN mm

EO® **Edmund Optics®**

TITLE 30mm DIA x 3.3mm THICKNESS, NIR COATED,
BOROFLOAT® WINDOW

DWG NO 12192

SHEET
1 OF 1