



NOTES:


1. COATING:
S1: METAL VELVET™
THICKNESS (μm) 5-8
2. ABSORBANCE: 99.9 (0 - 10° AOI)%
3. ABRASION RESISTANCE: LIGHT, DO NOT TOUCH
4. HUMIDITY RESISTANCE: MIL-C-48497A
5. OPERATING TEMPERATURE (°C): -40 to 150
6. WAVELENGTH RANGE: 0.3 - 14
7. TYPICAL ADHESIVE OUTGASSING PERFORMANCE:
0.85% TML
0% VCM
PER ASTM E595-77/84/90



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	Metal Velvet Low Outgassing Adhesive Foil Sheet 200 x 600mm	
ALL DIMS IN	mm	DWG NO	12516	SHEET 1 OF 1