





FOCAL LENGTH (EFL): 120 ±1,2  
BACK FOCAL LENGTH (BFL): 116,04

1 AR COATING: NONE

| LEFT SURFACE                                                                          |                          |             | MATERIAL                                                                            | RIGHT SURFACE                                                                                                 |                                                          |                  |
|---------------------------------------------------------------------------------------|--------------------------|-------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------|----------------------------------------------------------|------------------|
| R                                                                                     | 62,02±0,062 CX           |             | GLASS    N-BK7   517/642                                                            | R                                                                                                             | ∞ PL                                                     |                  |
| Øe                                                                                    | 29                       |             |                                                                                     | Øe                                                                                                            | 29                                                       |                  |
| 3/                                                                                    | 3 (0,5) λ=632,8 nm       |             |                                                                                     | 3/                                                                                                            | 3 (0,5) λ=632,8 nm                                       |                  |
| 4/                                                                                    | -                        |             |                                                                                     | 4/                                                                                                            | 1,93'                                                    |                  |
| 5/                                                                                    | 40 - 20 (MIL-PRF-13830B) |             |                                                                                     | 5/                                                                                                            | 40 - 20 (MIL-PRF-13830B)                                 |                  |
| 6/                                                                                    | -                        |             |                                                                                     | 6/                                                                                                            | -                                                        |                  |
| PROTECTIVE CHAMFERS AS NEEDED                                                         |                          |             | FIRST ANGLE<br>PROJECTION                                                           | <div> Edmund Optics®</div> |                                                          |                  |
| ROHS:<br>COMPLIANT                                                                    | SCALE:<br>NONE           | λ = 587,6nm |                                                                                     |                                                                                                               |                                                          |                  |
| SPECIFICATIONS SUBJECT TO CHANGE WITHOUT<br>NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY |                          |             |  | TITLE                                                                                                         | 30,0mm Dia, x 120,0mm FL, Uncoated,<br>Plano-Convex Lens |                  |
| FOR INFORMATION ONLY: DO NOT MANUFACTURE<br>PARTS TO THIS DRAWING                     |                          |             |                                                                                     | ALL DIMS<br>IN:                                                                                               | mm                                                       |                  |
| INDICATIONS IN ACCORDANCE WITH ISO 10110                                              |                          |             | DWG NO                                                                              |                                                                                                               | 45243                                                    | SHEET SIZE<br>A4 |
|                                                                                       |                          |             |                                                                                     |                                                                                                               |                                                          | SHEET<br>1 OF 1  |