
PN: MS-027-Q-Y-A



INPUT PARAMETER	
Wavelength [nm]:	532
Beam Mode (SM/MM):	SM or MM
Minimum Beam Diameter [mm]:	>0.37

ELEMENT PARAMETER	
Element Type:	Window
Material:	Fused Silica
Element Size [mm]:	25.4
Clear Aperture [mm]:	22.9
Thickness [mm]:	3
Coating:	AR/AR coating

OUTPUT PARAMETER	
Number of Spots:	9x9
Separation Angle [deg]:	0.25x0.25
Of [deg]:	2.00x2.00
Transmission efficiency:	Close to 100%
Overall Efficiency:	~ 73%
Uniformity (Contrast) [%]:	<13%
Zero-Order relative to the average [%]:	0-100%

Holo/Or can improve the performances of this item. Please send us your requirements