

1

2

3

4

5

6


7

8

REVISIONS

REV.	DESCRIPTIONS	EDIT BY	DATE:(d/m/y)
------	--------------	---------	--------------

MALE



PIN 1	BROWN	24V
PIN 2	WHITE	-
PIN 3	BLUE	GND
PIN 4	BLACK	-
PIN 5	GRAY	-



CONNECTOR

LED-LUX-50-16

COLOR	WAVELENGTH TOLERANCES
WHITE	6500k
RED	620-630nm
GREEN	520-535nm
BLUE	460-470nm
IR850	N/A
IR940	N/A
UV	N/A
RGB	N/A
RGBW	N/A

WAVELENGTH

ESTIMATE POWER RATING:	
VOLTAGE	24V
CURRENT	90mA
POWER	2.16W
WEIGHT	100g



TMS LITE
TMS LITE SDN. BHD.
LED ILLUMINATION SOLUTION PARTNER

DESIGN BY	NIZAM	UNIT: MM
CHECK BY	KB TAN	SIZE A4
DATE	14/2/2022	REVISION:
MATERIAL	-	01
FINISHING	-	SCALE:
QTY	-	1:1

PRODUCT SERIES: HBF SERIES

TITLE	DRAWING LAYOUT	GEN. TOLERANCES
PART NO	HBF-00-08-1-W-24V-M12	X ±0.15
DWG NO	-	X.X ±0.1
		X.XX ±0.05
		SHEET 1 OF 1

1

2

3

4

5

6

7

8