

FPQ3-120RD

Model name	FPQ3-120RD
LED color	Red
Input voltage	24 VDC
Power consumption(max.)	16 W
Weight(max.)	220 g
Connector	SMR-03V-B
Polarity and signal	1:(+) 2:NC 3:(-)

Unit: mm

