

FPQ3-120SW

Model name	FPQ3-120SW
LED color	White
Input voltage	24 VDC
Power consumption(max.)	27 W
Weight(max.)	220 g
Connector	SMR-03V-B
Polarity and signal	1:(+) 2:NC 3:(-)

Unit: mm

