

FPQ3-120BL

Model name	FPQ3-120BL
LED color	Blue
Input voltage	24 VDC
Power consumption(max.)	21 W
Weight(max.)	220 g
Connector	SMR-03V-B
Polarity and signal	1:(+) 2:NC 3:(-)

Unit: mm

