NOTES:

1. SUBSTRATE: FLOAT GLASS


2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: BBAR (425-700nm) R(AVG) ≤0.5% @ 425 - 700nm



3. FINE GRIND SURFACE

4. ROHS COMPLIANT



FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
Shape	PLANO	PLANO
SURFACE QUALITY	80 - 50	80 - 50
CLEAR APERTURE	Ø 45.00	Ø45.00
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

			U
THIRD ANGLE PROJECTION		TITLE	
ALL DIMS IN	mm	DWG NO	

B	Edmund Optics ®
TITLE	50mm Dia. x 3mm High Efficiency Window

MS IN mm DWG NO 21326 SHEET 3 OF 4