

LDQ-150IR2-~~850~~
940

Model Name	LDQ-150IR2-850/940
LED Color	Infrared
Input Voltage	24V DC(max.)
Power Consumption	16W(max.)
Weight	530g
Input Connector	SMR-03V-B
Polarity & Signal	1: (+), 2: NC, 3: (-)

Unit: mm

