

NOTES:

- 1. LASER CLASS:
IIIb
- 2. OPERATING TEMPERATURE: 15 to 30 °C
OPERATING VOLTAGE: 5V
- 3. OUTPUT POWER: 50mW
- 4. WAVELENGTH RANGE: 940±15 nm



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

| | | | | |
|---------------------------|----|--------|----------------------------------|-----------------|
| THIRD ANGLE PROJECTION | | TITLE | 940nm 50mW Pigtailed Laser Diode | |
| ALL DIMS IN | mm | DWG NO | 23795 | SHEET 1 OF 1 |