




NOTES:

- 1. SUBSTRATE: BOROFLOAT®
- 2. COATING (APPLY ACROSS CLEAR APERTURE):  
S1 & S2: NONE
- 3. FINE GRIND SURFACE
- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE FLATNESS	4 - 6λ	4 - 6λ
SURFACE QUALITY	80 - 50	80 - 50
CLEAR APERTURE	Ø 36.00	Ø 36.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN mm

**EO**® **Edmund Optics®**

TITLE	40mm Diameter x 3.3mm Thickness, Uncoated, BOROFLOAT® Window		
DWG NO	29391	SHEET	1 OF 1