





f': 10 ±0,1

BACK FOCAL LENGTH (BFL): 8,1



LEFT SURFACE			MATERIAL	RIGHT SURFACE													
R 5,17 CX Øe 6,3 λ AR R(880nm, 0°) ≤ 0,25% Rave(400nm - 870nm, 0°) ≤ 1,25% Rave(890nm - 1000nm, 0°) ≤ 1,25% 3/ 3 (0,5) λ=632,8 nm 4/ 5,8' 5/ 40 - 20 6/ - P			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 6,3 λ AR R(880nm, 0°) ≤ 0,25% Rave(400nm - 870nm, 0°) ≤ 1,25% Rave(890nm - 1000nm, 0°) ≤ 1,25% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - P													
PROTECTIVE CHAMFERS AS NEEDED <table><tr><td>ROHS: COMPLIANT</td><td>SCALE: NONE</td><td>λ = 587,6nm</td></tr></table> SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110				ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm	FIRST ANGLE PROJECTION ALL DIMS IN: mm	Edmund Optics® <table><tr><td>TITLE</td><td colspan="2">7mm Dia x 10mm FL, VIS-NIR Coated, Plano-Convex Lens</td></tr><tr><td>DWG NO</td><td>71305</td><td>SHEET SIZE A4</td></tr><tr><td></td><td></td><td>SHEET 1 OF 1</td></tr></table>		TITLE	7mm Dia x 10mm FL, VIS-NIR Coated, Plano-Convex Lens		DWG NO	71305	SHEET SIZE A4		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm															
TITLE	7mm Dia x 10mm FL, VIS-NIR Coated, Plano-Convex Lens																
DWG NO	71305	SHEET SIZE A4															
		SHEET 1 OF 1															