

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Industrial and Pointing Lasers](#)

Laboratory Laser Diode Modules



- Visible and Near IR Models
- Focusable from 20mm to Infinity



Common Specifications

General

Note:		Includes: Users Manual, Power Supply, Warning Label, and Focus Key	Type of Laser:		Diode
--------------	--	--------------------------------------------------------------------	-----------------------	--	-------

Optical Properties

Beam Size at Nearest Focus (µm):		25	Beam Diameter (mm):		4 x 2
Beam Divergence (mrad):		<0.5	Focus Range:		35mm - ∞

Hardware & Interface Connectivity

Power Supply:		110/240 V AC (included)	Output Type:		Free Space
----------------------	--	-------------------------	---------------------	--	------------

Technical Information

Products

Wavelength (nm)	Output Power (mW)	Beam Size at Nearest Focus (μm)	Beam Diameter (mm)	Beam Divergence (mrad)	Stock Number	Price	Buy
635.00	1 (Maximum)	25	4 x 2	<0.5	#53-227	₹31,500	10 to 12 days
670.00	3 ($\pm 5\%$)	25	4 x 2	<0.5	#39-569	₹27,000	10 to 12 days
850.00	3 ($\pm 5\%$)	25	4 x 2	<0.5	#53-760	₹36,000	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com