

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Spot Lights](#)

## Compact LED Spot Lights



- Variable Intensity with DC Current Controller
- Excellent Uniformity
- 60,000 Hour Product Lifetime
- [Heat Sinks and Power Supplies](#) Sold Separately

Common Specifications

General			
LED Lifetime (hours):	100,000	Type of Illumination:	LED Illuminator
Geometry:	Spot Light	Illumination Mode:	Strobed or Constant

Physical & Mechanical Properties			
Diameter (mm):	35.00	Height (mm):	29.5

Optical Properties			
Spot Size at 50mm Working Distance (mm):	10.00		



Electrical			
Maximum Input Current:	400mA		

Hardware & Interface Connectivity			
Power Supply:	Power Supply Required and Sold Separately: USA: <a href="#">#59-433</a> Europe: Not Available Japan: <a href="#">#59-433</a> Korea: Not Available China: <a href="#">#59-433</a>		

Threading & Mounting			
Mounting Threads:	M3		

## Technical Information

## Products

Color	Wavelength (nm)	Dia. (mm)	Stock Number	Price	Buy
<a href="#">#63-337 Clearance</a>					
					
Clearance					
Red	630.00	35.00	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹48,600	10 to 12 days
<a href="#">#63-339 Clearance</a>					
					
Clearance					
White	-	35.00	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹55,350	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)