

[All Products](#) / [Imaging Lenses](#) / [Telecentric Lenses](#)

High Resolution In-Line Illumination C-Mount Telecentric Lenses



- Designed for High Resolution Imaging
- In-line Illumination Port (0.312" Ferrule)
- 2/3" Max. Sensor Format

Common Specifications

General			
Series:	High Res In-Line Illumination C-Mnt Telecentric Lenses	Functionality:	Inline Illumination
Note:	Magnification Tolerance %: ±3	Compatible Light Guide/Source:	1/4" (0.312")
Optical Properties			
Maximum Image Circle (mm):		11.00	
Sensor			
Maximum Sensor Format:		2/3"	
Pixel Size (µm):		2.60	
Threading & Mounting			
Filter Thread:	N/A		
Mount:	C-Mount		

Technical Information

Products

PMAG	Max. Sensor Format	Aperture (f/#)	WD (mm)	Style	Stock Number	Price	Buy
0.19X	2/3"	f/6	110.00	In-Line Illumination	#65-026	₹3,89,250	10 to 12 days
1X	2/3"	f/7 - Closed	120.00	In-Line Illumination	#65-027	₹2,79,450	10 to 12 days
2X	2/3"	f/8 - Closed	100.00	In-Line Illumination	#65-028	₹3,19,500	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com