

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Spot Lights](#)

Advanced Illumination High Intensity LED Spot Lights See More

by [Advanced Illumination](#)



- 65mm Coverage at 300mm Working Distance
- M6 Thread for Mounting
- Variable Intensity and Strobed Options

Common Specifications

General

| | | | |
|------------------------------|--|------------------------------|-----------------------|
| LED Lifetime (hours): | 50,000 | Type of Illumination: | LED Illuminator |
| Note: | Optional Manual Intensity Adjustment #86-887 and #89-555 are Available | Manufacturer: | Advanced Illumination |
| Geometry: | Spot Light | | |

Physical & Mechanical Properties

| | | | |
|-----------------------------|-----------------|--------------------|-------|
| Height (mm): | 26.0 | | |
| Dimensions (mm): | 66.7 L x 62.0 W | Weight (g): | 122.5 |
| Field Coverage (mm): | 65.00 | | |

Optical Properties

| | |
|-----------------------------------|--------|
| Working Distance (inches): | 6 - 24 |
|-----------------------------------|--------|

Electrical

| | |
|---------------------------------|-------|
| Maximum Trigger Frequency (Hz): | 30.00 |
|---------------------------------|-------|

Hardware & Interface Connectivity

| | |
|------------|--------------|
| Connector: | Flying Leads |
|------------|--------------|

| | |
|------------------------|-------|
| Operating Voltage (V): | 24.00 |
|------------------------|-------|

| |
|---------------|
| Power Supply: |
|---------------|

Power Supply Required
and Sold Separately:
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

| | |
|--------------------|-------------------------------|
| Power Requirement: | 90 - 264 V AC @ 47 - 63 Hz |
|--------------------|-------------------------------|

| | |
|----------------------|-----|
| Length of Cable (m): | 1.5 |
|----------------------|-----|

Threading & Mounting

| | |
|-------------------|-----------------------------|
| Mounting Threads: | M4 Nut Channel for Mounting |
|-------------------|-----------------------------|

Technical Information

Products

| Dimensions (mm) | Color | Wavelength (nm) | Stock Number | Price | Buy |
|--------------------|-------|--------------------|-------------------------|---------|---------------|
| 66.7 L x 62.0 W | White | - | #86-429 | ₹51,480 | 10 to 12 days |
| 66.7 L x 62.0 W | Blue | 470.00 | #86-430 | ₹51,480 | Contact Us |
| 66.7 L x 62.0 W | Green | 530.00 | #86-431 | ₹51,480 | Contact Us |
| 66.7 L x 62.0 W | Red | 625.00 | #86-432 | ₹51,480 | 10 to 12 days |
| 66.7 L x 62.0 W | White | - | #86-433 | ₹70,290 | Contact Us |
| 66.7 L x 62.0 W | Blue | 470.00 | #86-434 | ₹70,290 | 10 to 12 days |
| 66.7 L x 62.0 W | Green | 530.00 | #86-435 | ₹70,290 | Contact Us |
| 66.7 L x 62.0 W | Red | 625.00 | #86-436 | ₹70,290 | Contact Us |



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com