

[All Products](#) /
 [Optomechanics](#) /
 [Motorized Translation Stages](#) /
 [Motorized Linear Stages](#)

Zaber™ High Precision Motorized Stage Systems [See More by Zaber™](#)



- High Accuracy, 25mm, 50mm, 100mm, and 200mm Travel Options
- Integrated Motor and Controller
- Available with Integrated, 200 Counts per Revolution (CPR) Motor Mounted Encoder
- Easily Configurable in X-Y or X-Y-Z Configurations
- Vacuum-Compatible Options

Common Specifications

General

Manufacturer:	Zaber Technologies Inc.	Type of Motor:	2-Phase Stepper
----------------------	-------------------------	-----------------------	-----------------

Physical & Mechanical Properties

Type of Movement:	Linear (X)	Guide System:	Needle Roller Bearing
Backlash (μm):	<12	Load Capacity (kg):	10
Repeatability (μm):	<3		

Electrical


Maximum Operating Current (mA):	350
--	-----

Technical Information

Device Overview / Connectors


Images are shown looking into the device.

Power


	Pin	Description
	1	24 - 48 V
	2	GND (Note: power supplies ground this pin to AC Earth)

Note: To prevent damage to the device due to static buildup, the device should be properly grounded. The power supplies for X-Series devices are non-isolated and thus ground the device chassis to Earth via the negative terminal of the power supply. If for any reason you are using an isolated power supply, please ensure your device is grounded by connecting the negative terminal of the power connector to AC Earth.


#68-645





#68-644





#68-343





Products

Stage Size (mm)	Type	Travel (mm)	Encoder	Stock Number	Price	Buy
#74-699 New						
						
New						
173.4 x 101.2	Metric	50.8	No	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹5,52,363	10 to 12 days
#74-700 New						
						
New						
224.2 x 152.0	Metric	101.6	No	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹5,82,552	10 to 12 days
45 x 162.6	Metric	25.4	-	#15-285	₹1,94,850	10 to 12 days
45 x 162.6	Metric	25.4	Yes	#22-217	₹2,17,800	10 to 12 days
45 x 188.0	Metric	50.8	-	#15-286	₹2,06,550	Contact Us
45 x 188.0	Metric	50.8	Yes	#22-218	₹2,29,500	Contact Us

45 x 238.8	Metric	101.6	-	#15-287	₹2,30,400	10 to 12 days
45 x 238.8	Metric	101.6	Yes	#22-219	₹2,53,350	10 to 12 days
45 x 340.4	Metric	203.2	-	#15-288	₹2,53,800	10 to 12 days
45 x 340.4	Metric	203.2	Yes	#22-220	₹2,76,750	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com