


[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Inline Lights](#)

Advanced Illumination Fiber Optic Replacement LED Spot Lights

See More by [Advanced Illumination](#)




- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Ports
- 50,000 Hour Lifetime
- Low Power Consumption



Common Specifications

General			
LED Lifetime (hours):	50,000	Type of Illumination:	LED Illuminator
Manufacturer:	Advanced Illumination	Geometry:	Spot Light
Illumination Mode:	Constant		
Physical & Mechanical Properties			
Diameter (mm):	7.90		
Length (mm):	38.10	Outer Diameter (inches):	0.312
Hardware & Interface Connectivity			
Connector:	Flying Leads	Power Supply:	Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855
Length of Cable (m):	1.5		

Technical Information



Products

Color	Wavelength (nm)	Dia. (mm)	Stock Number	Price	Buy
#87-543 Clearance					
					
Clearance					
Green	520.00	7.90	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹18,450	Contact Us
#87-544 Clearance					
					
Clearance					
Red	660.00	7.90	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹18,450	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 :
www.edmundoptics.com