

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Bar Lights](#)

## Advanced Illumination EuroBrite™ Bar Lights [See More by Advanced Illumination](#)



- Daisy Chain up to Four Units
- Requires No Heat Sink
- Available in White, Red, and Blue

# Common Specifications

General			
Operating Lifetime (hours):	50,000	Type of Illumination:	LED Illuminator
Note:	See Technical Information Tab for Typical Intensity	Manufacturer:	Advanced Illumination
Geometry:	Bar Light	Illumination Mode:	Strobed or Constant
Physical & Mechanical Properties			
Dimensions (mm):	300 x 64 x 30	Weight (g):	241.00
Electrical			
Maximum Input Current:	0.42 - 0.49A	Analog Intensity Control:	10% @ 0.7V, 100% @ 10V
Trigger-to-Pulse Latency:	10µm		
Hardware & Interface Connectivity			
Connector:	Flying Leads		
Input Voltage (V):	24V nominal (min. 22 / max. 28)	Power Supply:	Power Supply Required and Sold Separately: USA: <a href="#">#66-855</a> Europe: <a href="#">#66-855</a> Japan: <a href="#">#89-513</a> Korea: <a href="#">#33-773</a> China: <a href="#">#66-855</a>
Environmental & Durability Factors			
Operating Temperature (°C):	0 - 60	Environmental Rating:	IP67

## Technical Information

## Products

Dimensions (mm)	Color	Wavelength (nm)	Stock Number	Price	Buy
300 x 64 x 30	White	-	<a href="#">#33-444</a>	₹35,100	10 to 12 days
300 x 64 x 30	Red	625.00	<a href="#">#33-445</a>	₹35,100	10 to 12 days
300 x 64 x 30	Blue	470.00	<a href="#">#33-446</a>	₹67,500	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)