

[All Products](#) / [Optomechanics](#) / [Benchtop Optical Mounts](#) / [Polarizer Mounts](#)

TECHSPEC® Rotation Kinematic Mounts



- 360° Continuous Optic Rotation
- 25.4mm Centerline Height
- 5° Graduations

Common Specifications

General	
Type of Optics:	Circular

Physical & Mechanical Properties			
Construction:		Aluminum plates, stainless steel screws, and brass thread bushings	
Fine Tilt Angle (°):		±5	Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec):		4	Adjustment Screw Pitch (mm): 0.25
Min. Thickness of Compatible Optics (mm):		1.8	Pointing Stability (μrad): 1.3

Optical Properties	
Angle Tolerance (°):	0.4 per 0.25mm turn

Threading & Mounting	
Compatible Post:	M4 x 0.7, 8-32

Environmental & Durability Factors	
Thermal Stability (μrad):	<5

Technical Information

Products

Size of Compatible Optics (mm)	Number of Adjustment Screws	Stock Number	Price	Buy
12.5 - 12.7	2	#36-637	₹11,223 Volume Pricing	20+ In Stock
25.0 - 25.4	2	#36-635	₹11,956 Volume Pricing	15 In Stock
12.5 - 12.7	3	#36-638	₹12,616 Volume Pricing	15 In Stock
25.0 - 25.4	3	#36-636	₹13,203 Volume Pricing	8 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com