

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Visible Windows](#)

# SCHOTT AS 87 ECO Ultra-Thin Windows

See More by [SCHOTT Optical Components](#)



- High Level of Flexibility
- Ultra-Thin Thickness for Low Profile Designs
- Excellent Transmission from 250nm to >3μm

## Common Specifications

### Physical & Mechanical Properties

<b>Bevel:</b>	Protective as needed	<b>Clear Aperture (%):</b>	90
<b>Thickness (mm):</b>	0.10 ±0.01	<b>Knoop Hardness (kg/mm<sup>2</sup>):</b>	500
<b>Poisson's Ratio:</b>	0.216	<b>Young's Modulus (GPa):</b>	73.3

### Optical Properties

<b>Abbe Number (v<sub>d</sub>):</b>	59.5	<b>Coating:</b>	Uncoated
<b>Index of Refraction (n<sub>d</sub>):</b>	1.504	<b>Substrate:</b>	<a href="#">AS 87 ECO</a>
<b>Surface Quality:</b>	80-50	<b>Wavelength Range (nm):</b>	200 - 3200

### Material Properties

<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>	8.7	<b>Density (g/cm<sup>3</sup>):</b>	2.46
---	-----	------------------------------------	------

## Technical Information

Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
-	5.00 x 5.00	0.10	Uncoated	<a href="#">#20-199</a>	₹2,054 Qty 11+ ₹1,632	10 to 12 days
-	10.00 x 10.00	0.10	Uncoated	<a href="#">#12-292</a>	₹2,292 Qty 11+ ₹1,834	10 to 12 days
-	10.00 x 20.00	0.10	Uncoated	<a href="#">#12-293</a>	₹2,292 Qty 11+ ₹1,834	10 to 12 days
-	10.00 x 30.00	0.10	Uncoated	<a href="#">#12-294</a>	₹2,292 Qty 11+ ₹1,834	10 to 12 days
-	10.00 x 50.00	0.10	Uncoated	<a href="#">#12-295</a>	₹2,751 Qty 11+ ₹2,201	10 to 12 days
-	10.00 x 100.00	0.10	Uncoated	<a href="#">#12-296</a>	₹2,751 Qty 11+ ₹2,201	10 to 12 days

[#12-298 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

-	12.70 x 25.40	0.10	Uncoated		₹2,970 Qty 11+ ₹2,475	10 to 12 days
---	---------------	------	----------	--	--------------------------	---------------

### [#12-311 Clearance](#)



#### Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

-	12.70 x 63.50	0.10	Uncoated		₹3,420 Qty 11+ ₹2,858	10 to 12 days
---	---------------	------	----------	--	--------------------------	---------------

-	20.00 x 20.00	0.10	Uncoated	<a href="#">#20-200</a>	₹2,439 Qty 11+ ₹1,944	10 to 12 days
---	---------------	------	----------	-------------------------	--------------------------	---------------

-	25.40 x 25.40	0.10	Uncoated	<a href="#">#12-313</a>	₹2,751 Qty 11+ ₹2,201	10 to 12 days
---	---------------	------	----------	-------------------------	--------------------------	---------------

-	25.40 x 50.80	0.10	Uncoated	<a href="#">#12-314</a>	₹2,751 Qty 11+ ₹2,201	10 to 12 days
---	---------------	------	----------	-------------------------	--------------------------	---------------

-	25.40 x 76.20	0.10	Uncoated	<a href="#">#12-315</a>	₹2,751 Qty 11+ ₹2,201	10 to 12 days
---	---------------	------	----------	-------------------------	--------------------------	---------------

-	25.40 x 127.00	0.10	Uncoated	<a href="#">#12-316</a>	₹3,282 Qty 11+ ₹2,641	10 to 12 days
---	----------------	------	----------	-------------------------	--------------------------	---------------

### [#12-317 Clearance](#)



#### Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

-	25.40 x 254.00	0.10	Uncoated		₹4,320 Qty 11+ ₹3,600	10 to 12 days
-	30.00 x 30.00	0.10	Uncoated	<a href="#">#20-201</a>	₹2,677 Qty 11+ ₹2,127	10 to 12 days
-	40.00 x 40.00	0.10	Uncoated	<a href="#">#20-202</a>	₹2,677 Qty 11+ ₹2,127	10 to 12 days
-	50.00 x 50.00	0.10	Uncoated	<a href="#">#20-203</a>	₹2,897 Qty 11+ ₹2,329	10 to 12 days
-	50.80 x 76.20	0.10	Uncoated	<a href="#">#20-204</a>	₹3,282 Qty 11+ ₹2,641	10 to 12 days
-	50.80 x 127.00	0.10	Uncoated	<a href="#">#20-205</a>	₹3,668 Qty 11+ ₹2,934	10 to 12 days
-	50.80 x 254.00	0.10	Uncoated	<a href="#">#20-206</a>	₹4,108 Qty 11+ ₹3,301	10 to 12 days
5.00	-	0.10	Uncoated	<a href="#">#20-207</a>	₹2,054 Qty 11+ ₹1,632	10 to 12 days
10.00	-	0.10	Uncoated	<a href="#">#20-208</a>	₹2,292 Qty 11+ ₹1,834	10 to 12 days
12.50	-	0.10	Uncoated	<a href="#">#20-209</a>	₹2,292 Qty 11+ ₹1,834	10 to 12 days
15.00	-	0.10	Uncoated	<a href="#">#20-210</a>	₹2,292 Qty 11+ ₹1,834	10 to 12 days
20.00	-	0.10	Uncoated	<a href="#">#20-211</a>	₹2,439 Qty 11+ ₹1,944	10 to 12 days

25.00	-	0.10	Uncoated	<a href="#">#20-212</a>	₹2,439 Qty 11+ ₹1,944	10 to 12 days
30.00	-	0.10	Uncoated	<a href="#">#20-213</a>	₹2,677 Qty 11+ ₹2,127	10 to 12 days
40.00	-	0.10	Uncoated	<a href="#">#20-214</a>	₹2,677 Qty 11+ ₹2,127	10 to 12 days
50.00	-	0.10	Uncoated	<a href="#">#20-215</a>	₹2,897 Qty 11+ ₹2,329	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)