

[All Products](#) / [Microscopy](#) / [Infinity Corrected Objectives](#)

ZEISS EC Epiplan Plan Achromat Infinity Corrected Objectives

See More by [ZEISS](#)




- Ideal for Brightfield, Fluorescence, and Differential Interference Contrast Applications
- Enhanced Contrast
- Excellent Color Correction and Flatness of Field

Common Specifications

General			
Compatible Tube Lens Focal Length (mm):		Focal Length: 164.50mm	
Manufacturer:		Zeiss	
Physical & Mechanical Properties			
Maximum Diameter (mm):		30	
Optical Properties			
Compatible Cover Glass Thickness (mm):		N/A	
Wavelength Range (nm):		480 - 650	
Field Number (mm):		23	
Parfocal Length (mm):		45	
Immersion Liquid:		N/A	
Threading & Mounting			
Mounting Threads:		M27 x 0.75	
Environmental & Durability Factors			
Operating Temperature (°C):		+10 to +40	
Operating Humidity:		75% at 35°C	

Technical Information



Products

Magnification	NA	Field Number (mm)	FL (mm)	Model Number	WD (mm)	Stock Number	Price	Buy
5X	0.13	23	33.00	422030-9902-000	11.8	#13-822	₹53,100	10 to 12 days
10X	0.25	23	16.50	422040-9902-000	11	#13-823	₹53,100	10 to 12 days
20X	0.4	23	8.20	422050-9903-000	3.2	#13-824	₹75,600	10 to 12 days
40X	0.6	23	4.10	422060-9901-000	2.2	#13-825	₹91,350	10 to 12 days
50X	0.75	23	3.30	422070-9902-000	1	#13-826	₹98,550	10 to 12 days
100X	0.85	23	1.60	422090-9902-000	0.87	#13-827	₹1,37,700	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 :
www.edmundoptics.com