

[All Products](#) / [Laser Optics](#) / [Laser Optical Assemblies](#) / [F-Theta Lenses](#)

Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses See

More by [Jenoptik](#)



- Low-Absorption Fused Silica Substrates for High-Power Laser Applications
- Large Scan Fields Up to 328mm x 328mm
- High Damage Thresholds and Low Telecentricity Errors
- [Jenoptik JENar™ F-Theta Scanning Lenses](#) Also Available

Common Specifications

General

Manufacturer: Jenoptik

Optical Properties

Substrate: [Fused Silica](#) (Corning 7980)

Threading & Mounting

Mounting Threads: M85 x 1

Technical Information

Products

Wavelength Range (nm)	Scan Angle (°)	Scan Field (mm)	Type	FL (mm)	Stock Number	Price	Buy
355	±20.1	50 x 50	JENar Silverline F-Theta	103.00	#16-768	₹2,92,050	Contact Us
355	±25	100 x 100	JENar Silverline F-Theta	170.00	#16-771	₹6,12,000	1 In Stock
355	±25.7	328 x 328	JENar Silverline F-Theta	510.00	#17-026	₹3,81,600	4 In Stock
900 - 1100	±20	78 x 78	JENar Silverline F-Theta	160.00	#17-021	₹6,84,900	1 In Stock
900 - 1100	±18	114 x 114	JENar Silverline F-Theta	255.00	#17-022	₹7,08,300	4 In Stock
1030 - 1080	±20	78 x 78	JENar Silverline F-Theta	160.00	#16-769	₹4,31,550	1 In Stock
1030 - 1080	±18	114 x 114	JENar Silverline F-Theta	255.00	#16-770	₹4,69,350	4 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com