

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Spot Lights](#)

Advanced Illumination Ethernet Controlled High Intensity In-Line Lights

See More by [Advanced Illumination](#)



- Controllable via Ethernet GUI or Web Browser
- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Ports
- Efficient Thermal Management for Long LED Life
- Compatible with [TECHSPEC® Telecentric Backlight Illuminators](#) and [Lenses](#)

Common Specifications

General			
LED Lifetime (hours):	50,000	Number of LEDs:	1
Type of Illumination:	LED Illuminator	Note:	Required Controller #18-645 ; Required Power Supply #66-855
Manufacturer:	Advanced Illumination	Geometry:	Spot Light
Illumination Mode:	Constant, Pulsed, Gated		
Physical & Mechanical Properties			
Weight (g):	85.1		
Hardware & Interface Connectivity			
Connector:	C1	Power Supply:	Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855
Length of Cable (m):	2		
Environmental & Durability Factors			
Operating Temperature (°C):	0 to +60		

Technical Information

Products

Color	Wavelength (nm)	Stock Number	Price	Buy
UV	365.00	#21-356	₹60,750	10 to 12 days
UV	395.00	#21-357	₹60,750	10 to 12 days
Blue	455.00	#21-358	₹50,400	10 to 12 days
Green	530.00	#21-359	₹50,400	10 to 12 days
Red	625.00	#21-360	₹50,400	10 to 12 days
IR	850.00	#21-361	₹50,400	10 to 12 days
IR	940.00	#21-362	₹50,400	Contact Us
White	-	#21-363	₹50,400	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 :
www.edmundoptics.com