

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Backlights](#)

Effilux High Power LED Backlights



- >90% Uniformity
- Integrated Analog Controller for Precise Intensity and Dimming
- Anti-Reflection System to Absorb Stray Light

Common Specifications

General

Type of Illumination:	LED illumination	Uniformity (%):	>90%
Manufacturer:	Effilux	Geometry:	Backlight
Illumination Mode:	Continuous with AIC (Analog Intensity Control)		

Hardware & Interface Connectivity

Power Supply:

Power Supply Required and Sold Separately:

USA: [#15-874](#)

Europe: [#15-875](#)

Japan: [#73-409](#)

Korea: [#73-409](#)

China: [#15-874](#)

Environmental & Durability Factors

Operating Temperature (°C):	0 - 50
------------------------------------	--------

Technical Information

Products

Color	Active Area (mm)	Stock Number	Price	Buy
White	200 x 200	#22-098	₹67,500	10 to 12 days
Red	200 x 200	#22-099	₹67,500	10 to 12 days
Blue	200 x 200	#22-100	₹67,500	10 to 12 days
White	300 x 300	#22-101	₹1,11,150	10 to 12 days
Red	300 x 300	#22-102	₹1,11,150	10 to 12 days
Blue	300 x 300	#22-103	₹1,11,150	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com