

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

TECHSPEC® HP+ Series Fixed Focal Length Lenses



- 1.2", C-Mount Lenses
- Up to 24.5 MegaPixels, 2.74µm Pixel Size Sensors
- 16mm to 35mm Focal Length

Common Specifications

General			
Series:	HP+ Series	Imaging Lens Type:	High Performance Lens
Physical & Mechanical Properties			
Iris Option:	Variable		
Optical Properties			
Maximum Image Circle (mm):	19.30		
Coating:	$\lambda/4$ MgF ₂	Coating Specification:	$\lambda/4$ MgF ₂
Sensor			
Maximum Sensor Format:	1.2"	Pixel Size (μm):	2.74
Threading & Mounting			
Mount:	C-Mount		
Environmental & Durability Factors			
Storage Temperature (°C):	-20 to +60 For questions regarding operating temperature please contact our support team		

Technical Information

Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
16.00	1.2"	f/2.8 – 16	100 - ∞	C- Mount	#20-225	₹74,385	3 In Stock
25.00	1.2"	f/2.8 – 22	200 - ∞	C- Mount	#20-226	₹70,079	1 In Stock
35.00	1.2"	f/2.8 – 16	200 - ∞	C- Mount	#20-227	₹70,079	1 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com