

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Metrology Lasers](#)

Coherent® Surelock™ Mini-Benchtop Laser Systems [See More](#)

by [Coherent®](#)



- Narrow 0.07nm FWHM Spectral Linewidth
- Extreme Temperature Insensitivity
- Ultra-Compact, Easy-to-Use Turnkey Laser System

Common Specifications

General

Note:	Recommended Fiber Patchcord: #23-706
-------	--

Physical & Mechanical Properties

Dimensions (mm):	150 x 150 x 50
Weight (kg):	1.00

Optical Properties

Numerical Aperture NA:	0.22
Spectral Line Width (nm):	0.07

Electrical

Input Current (A):	1.00
--------------------	------

Hardware & Interface Connectivity

Connector:	FC/PC	Input Voltage (V):	90 - 240 (AC)
------------	-------	--------------------	---------------

Environmental & Durability Factors

Operating Temperature (°C):	+10 to +35	Storage Temperature (°C):	-10 to +60
-----------------------------	------------	---------------------------	------------

Technical Information

Products

Title	Stock Number	Price	Buy
638nm SureLock Narrow Linewidth MM Fiber Coupled Laser	#70-754	₹5,03,100	10 to 12 days
785nm SureLock Narrow Linewidth MM Fiber Coupled Laser	#70-755	₹4,94,100	10 to 12 days
830nm SureLock Narrow Linewidth MM Fiber Coupled Laser	#70-756	₹5,12,100	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com