

[See all 2 Products in Family](#)

0 - 0.47", IDS Digimatic ABSOLUTE Thickness Gauge

See More by [Mitutoyo](#)



Stock **#78-347** **1 In Stock**

-

1

+

MRP ₹38,126

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹38,126 each
Need More?	Request Quote

Product Downloads

Accuracy (inches):	
±0.001	
General	
Range:	
0 - 0.47 inches	
Model Number:	
547-520S	
Physical & Mechanical Properties	
Resolution (inches):	
0.0005	

Regulatory Compliance	
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- 0 – 0.5" Range with 0.0005" Resolution
- Easy-To-Read Digital LCD Display
- ABSOLUTE® Linear Scale Eliminates Need for Zeroing

Mitutoyo Thickness Gauges are designed to quickly measure the thickness of different materials or objects with high accuracy of ±0.001". An ABSOLUTE® linear scale eliminates the need for setting the origin point every time the gauge is powered on and prevents over speed errors. These thickness gauges feature ceramic spindles and anvils for high corrosion resistance and waterproof data output connectors to protect against dust, water, and oil ingress. Mitutoyo Thickness Gauges are ideal for quick inspection of a wide range of materials and objects including paper, film, wire, sheet metal, leather, and plastic parts. The grip handle, easy-to-reach lifting lever, spring-loaded spindle, and LCD display allow for quick, easy, and accurate measurements.