

[See all 12 Products in Family](#)

# (0-1" Range), 0.0001", Uni-Mike Mechanical Outside Micrometer, Interchangeable Anvils

See More by [Mitutoyo](#)



Stock #78-306 **1 In Stock**

- 1 + MRP ₹31,966

Price inclusive of all taxes

**ADD TO CART**

#### Volume Pricing

Qty 1+	₹31,966 each
Need More?	<a href="#">Request Quote</a>

Note: This item requires accessories for use | [Learn More](#)

#### Product Downloads

Accuracy (inches):  
±0.002

#### General

Range:  
0 - 1 inches

Model Number:  
117-107

#### Physical & Mechanical Properties

---

0.0001 **Graduation (inches):**

---

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

---

Japan **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

---

## Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
- Measurement Ranges from 0 – 6"
- Baked Enamel Finish on Frame for Durability

Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mke Micrometer features interchangeable anvils ranging from 0-1" for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.

---

;