

[See all 12 Products in Family](#)

(0-13mm Range), 0.01mm Increment, Metric Micrometer Head

See More by [Mitutoyo](#)



Stock #78-313 **1 In Stock**

- 1 + MRP ₹9,293

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹9,293 each
Need More?	Request Quote

Product Downloads

General

0 - 13mm **Range:**

148-801-10 **Model Number:**

Physical & Mechanical Properties

±2 **Accuracy (µm):**

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Japan

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
- Measurement Ranges from 0 – 6"
- Baked Enamel Finish on Frame for Durability

Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mke Micrometer features interchangeable anvils ranging from 0-1" for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.