

[See all 12 Products in Family](#)

(0-3" Range), 0.0001", Mechanical Outside Micrometer, Set of 3

See More by [Mitutoyo](#)



Stock **#78-305** **1 In Stock**

-

1

+

MRP ₹60,534

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹60,534 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads	
±0.001	Accuracy (inches):
General	
0 - 3 inches	Range:
103-922	Model Number:
Contents of Kit:	

Outside Micrometer with Friction Thimble: 0-1"
Outside Micrometer with Friction Thimble: 1-2"
Outside Micrometer with Ratchet Stop: 2-3"
2 Micrometer Standards

Physical & Mechanical Properties

0.0001Graduation (inches):

Regulatory Compliance

ViewCertificate of Conformance:

JapanCountry of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
- Measurement Ranges from 0 – 6"
- Baked Enamel Finish on Frame for Durability

Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mke Micrometer features interchangeable anvils ranging from 0-1" for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.