

[See all 12 Products in Family](#)

(0-3" Range), 0.0001", Mechanical Outside Micrometer, Set of 3

See More by [Mitutoyo](#)



Stock **#78-305** **1 In Stock**

-

1

+

 ₹45,900

ADD TO CART

Volume Pricing	
Qty 1+	₹45,900 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

±0.001 **Accuracy (inches):**

General

0 - 3 inches **Range:**

103-922 **Model Number:**

Contents of Kit:
Outside Micrometer with Friction Thimble: 0-1"
Outside Micrometer with Friction Thimble: 1-2"

Physical & Mechanical Properties

0.0001
Graduation (inches):

Regulatory Compliance

View
Certificate of Conformance:

Japan
Country of Origin:

Edmund Optics India Private Limited
Imported By:

Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
 - Measurement Ranges from 0 – 6"
 - Baked Enamel Finish on Frame for Durability
- Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mike Micrometer features interchangeable anvils ranging from 0-1" for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.