

[See all 11 Products in Family](#)

0.25" Travel, 0.001" Grad. Mic. Drive S-Face



Drive Mechanisms

Stock **#87-093** **1 In Stock**

- 1 + MRP ₹8,677

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹8,677 each
Need More?	Request Quote

Product Downloads

General

English **Type:**

Mtutoyo **Manufacturer:**

148-206-10 **Model Number:**

Physical & Mechanical Properties

0.25 **Travel (inches):**

0.001	Graduation (inches):
3.5	Stem Diameter (mm):
Plain/Spherical	Stem/Spindle:
5	Stem Length (mm):
2	Spindle Diameter (mm):
6.5	Min. Spindle Length (mm):
6	Max. Diameter (mm):
32	Overall Length (mm):

Hardware & Interface Connectivity

English Micrometer	Type of Drive:
--------------------	-----------------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000	Imported By:

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
- Compatible with our [Ball Bearing Stages](#)

These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.

Please reference individual product descriptions to see which stages are compatible with each drive mechanism.