

0.3 OD, 25mm Dia., AR Coated, IR Neutral Density Filter



Infrared (IR) Neutral Density (ND) Filters

Stock **#12-243** 10 TO 12 DAYS

- 1 + **₹38,976.00**

ADD TO CART

Qty 1-10
₹38,976.00
Qty 11+
₹35,018.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm): 25.00 ±0.2
Optical Density OD (Average): 0.3
Substrate: ☐ Germanium (Ge)
Coating:

Metallic Based ND
Surface Quality: 80-50
Thickness (mm): 1.00 ±0.2
Transmission (%): 50.0
Transmission Tolerance (%): ±4.0
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 5800 - 6400
Parallelism (arcmin): <10
Clear Aperture (%): 90
Wavelength Range (µm): 5.8 - 6.4
Surface Flatness (P-V): 3 - 5λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant