

0.3 OD M39.0 x 0.50, Mounted Absorptive ND Filter



Stock **#59-166** 10 TO 12 DAYS

-

1

+

₹3,741.00

ADD TO CART

Qty 1-9
₹3,741.00
Qty 10+
₹3,532.00
Volume Pricing
Request Quote

Get Product Downloads
Optical Density OD (Average): 0.3
Clear Aperture CA (mm): 34.0
Filter Thread: M39 x 0.50
Substrate: ND Filter Glass

Thickness with Mount (mm): 5.00
Surface Quality: 80-50
Transmission (%): 50
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 5.2 ±0.3
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 41.0 ±0.3
Mount Thickness Including Threads (mm): 7

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View