

0.3 OD M52.0 x 0.75, Mounted Absorptive ND Filter



Stock #54-730 CLEARANCE 10 TO 12 DAYS

-

1

+

 ₹3,040.65

ADD TO CART

Qty 1+
₹3,040.65

Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average): 0.3
Clear Aperture CA (mm): 48.0
Filter Thread: M52 x0.75
Substrate: ND Filter Glass
Thickness with Mount (mm): 5.00

Surface Quality: 80-50
Transmission (%): 50
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 3.8 ±0.1
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 54.0 +0/-0.2
Mount Thickness Including Threads (mm): 6.3

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View