

0.35mm Dia, 670-1550nm, 0.0mm WD, Uncoated, GRIN Lens



Stock #88-355

10 TO 12 DAYS

-

1

+

₹7,134.00

ADD TO CART

Qty 1-10
₹7,134.00
Qty 11+
₹6,308.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
0.35 +0.00/-0.01

Effective Focal Length EFL (mm):
0.30

Substrate:
Aluminosilicate Glass Embedded with Silver Ions

f#:
0.86

Numerical Aperture NA: 0.58
Coating: Uncoated
Type: Gradient Index Lens
Focal Length Specification Wavelength (nm): 670 - 1550
Gradient Constant (mm⁻¹): 2.02
Index of Refraction n_d - Center of Lens: 1.62
Length (mm): 0.78
Pitch: 0.25
Surface Quality: 40-20
Working Distance (mm): 0
Working Distance Tolerance (mm): ±0.01
Length Tolerance (%): ±5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View