

0.5 OD, 25.4mm Dia., Reflective Neutral Density Filter



Stock #27-928 CLEARANCE [CONTACT US](#)

-

1

+

₹1,301.00

ADD TO CART

Qty 1+
₹1,301.00

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.40 ±0.3

Optical Density OD (Average):
0.5

Substrate: ☐
Borosilicate

Coating:
Metallic Based ND

Thickness (mm):
1.00

Thickness Tolerance (mm): ±0.25
Transmission (%): 32.00
Type: Neutral Density Filter
Parallelism (arcmin): ±3
Dimensional Tolerance (mm): ±0.3
Clear Aperture (%): >90
Optical Density Tolerance (%): ±10

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View