

TECHSPEC® 0.5 OD 25mm Dia UV-NIR ND Filter



UV-NIR Neutral Density Filters

Stock **#88-271** 10 TO 12 DAYS

- 1 + **₹14,529.00**

ADD TO CART

Qty 1-5
₹14,529.00
Qty 6+
₹13,033.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Optical Density OD (Average):
0.5

Substrate: [Fused Silica](#) (Corning 7980)

Coating: Metallic Based ND
Surface Quality: 40-20
Thickness (mm): 3.00 ±0.10
Transmission (%): 32.0
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 190 - 1700
Clear Aperture (%): 80.00
Transmitted Wavefront, P-V: λ/4
Optical Density Tolerance (%): ±10
Parallelism (arcsec): <5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View