

0.50" Travel, 0.001" Grad, Micrometer Drive Mech



Drive Mechanisms

Stock **#58-660** [CONTACT US](#)

-

1

+

₹13,224.00

ADD TO CART

Qty 1+
₹13,224.00

Volume Pricing
Request Quote

Get Product Downloads

Type of Drive: English Micrometer
Type: English
Travel (inches): 0.5
Graduation (inches): 0.001
Manufacturer: PARKER-HANNIFIN

Stem Diameter (mm): 9.5
Stem/Spindle: Plain/Flat
Stem Length (mm): 9.5
Spindle Diameter (mm): 6.6 (0.26")
Min. Spindle Length (mm): 6.35 (0.25")
Max. Diameter (mm): 13.7 (0.54")
Overall Length (mm): 60.5 (2.38")

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View

