

[See all 11 Products in Family](#)

0.50" Travel, 0.001" Grad, Micrometer Drive Mech



Drive Mechanisms

Stock #58-660 **14 In Stock**

MRP ₹19,472

! Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-9	₹19,472 each
Qty 10-24	₹17,524 each
Need More?	Request Quote

Product Downloads

General

English **Type:**

PARKER-HANNIFIN **Manufacturer:**

Physical & Mechanical Properties

0.5 **Travel (inches):**

0.001	Graduation (inches):
9.5	Stem Diameter (mm):
Plain/Flat	Stem/Spindle:
9.5	Stem Length (mm):
6.6 (0.26")	Spindle Diameter (mm):
6.35 (0.25")	Min. Spindle Length (mm):
13.7 (0.54")	Max. Diameter (mm):
60.5 (2.38")	Overall Length (mm):

Hardware & Interface Connectivity

English Micrometer	Type of Drive:
--------------------	-----------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
 - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential. Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

Technical Information

