

TECHSPEC® 0.5" Dia. Protected Gold, λ /20 Flat Fused Silica



Stock **#43-400-566** 10 TO 12 DAYS

- 1 + **₹12,702.00**

ADD TO CART

Qty 1-10
₹12,702.00
Qty 11+
₹11,484.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
 λ /20 (measured before coating)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Diameter (mm): 12.70 +0.0/-1.02
Diameter Tolerance (inches): +0.0/-0.04
Substrate: Fused Silica (Corning 7980)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 11.43
Note: Flatness is specified as Peak to Valley
Thickness (mm): 3.20 ±0.8
Thickness Tolerance (mm): ±0.8
Type: Flat Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant